



[🏠 Home](#) > [Product Information](#) > [HBV680M1VTR-0608](#)

Series | Type: [HBV](#) | [SMD](#)

Part Number	HBV680M1VTR-0608	
Type	SMD	Polar
Series	HBV	
Temperature Range	-55 ~ 105	°C
Voltage	35	V, DC
Capacitance	68	μF, 120 Hz
Tolerance	-20 ~ 20	%
Diameter	6.3	0.5 (β)mm
Length	7.7	0.3 (α)mm
Tanδ	11m	120 Hz
Leakage Current	23.8	μA, 2 min.
ESR		mΩ, Hz
Impedance/20°C	0.035	Ω, 100k Hz
Impedance/-10°C		Ω, Hz
Ripple Current		mA, Hz
Ripple Current	2000	mA, 100k Hz
Endurance	10000	Hours at 105 °C
Coating/Sleeve	PET Coating	
Packaging	Reel	
Pack Quantity	1000	Pieces
Carton Quantity	10000	Pieces

Part Search

