

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH — BASIC

CATALOG LISTING
V7-3A17D8-000-3

CW-B0302

CATALOG LISTING
V7-3A17D8-000-3

M

ISSUE
5

REPLACES

RELEASE NO. PR-18122

CHECK

REVISIONS

A	CO-67704	JAP	18 JUN 90
B	CO-67929	WLS	12 OCT 90
C	CO-69198	BAB	7 MAR 91
D	CO-76104	GRT	4 OCT 93

CHECK

3 APR 90

JAP


CHECK

3 APR 90

WLS

3 APR 90


WLS



NOTE
1 — SWITCH WILL OPERATE AND RELEASE WITHIN FULL EXCURSION OF THE PLUNGER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE — — 60 GRAMS MAX	CONTACT ARRANGEMENT	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE — — — 11 GRAMS MIN	S P D T			
OVERTRAVEL — — — — .050 MIN	L162 5A 125, 250, 277 VAC	ONE PLACE (.01)	± .030	
RELEASE TRAVEL — — — — .010 MIN	1/10HP 250 VAC	TWO PLACE (.00)	± .015	
		THREE PLACE (.000)	± .005	
		ANGLES	±	
		WEIGHT		

