## Product Line

- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
  - M20
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub








# LC20-03PMFS-SN8001

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Metal, Shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

## Mating Pair & Accessories

Connector Type

Search



Heavy Duty Shielded,...



Heavy Duty Shielded,...



M Series, Accessory,...
CAP-WHBMSPD1

− 0 +

− 0 +

− 0 +

Add to Cart | Inquiry

**Specifications** | Download / CAD

| | |
|---|---|
| Nominal Current<br>**20A** | Connector Type<br>**Receptacle** |
| Shielded<br>**Metal, Shielded** | No. of Contacts<br>**03** |
| Connector Gender<br>**Male** | Backshell<br>**Square** |
| Mating Style<br>**Screw Thread** | IP Rating<br>**IPX8** |
| Assembly Style<br>**Solder** | |

More Options

### People Also Bought



Downloaded from Arrow.com.