



Part Number : [1301080121](#)

Product Description : Super-Safeway 13W
Fluorescent Machine Light, Screw Mount 24V with 18/3
SJTOOW Cord Type, Overall Cord Length 4.57m (15.0')

Series Number : 130108

Status : Active

Product Category : Lamps and Lights

Engineering Number : 1083-3MM-24



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130108
Description	Super-Safeway 13W Fluorescent Machine Light, Screw Mount 24V with 18/3 SJTOOW Cord Type, Overall Cord Length 4.57m (15.0')
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678867258

Electrical

Lamp Wattage - Maximum	13W
Lumens	900
On/Off Switch	Yes
Voltage (Fixture) - Maximum	24V DC

Physical

Bulb Type	Fluorescent
Cord Length - Primary	4.57m (15.0')
Cord Length - Secondary	N/A
Cord Type - Primary	18/3 SJTOOW
Depth	76.20mm (3.000")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	57.15mm (2.250")
Lamp Type	PL13/41
Length	552.45mm (21.750")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Magnetic-Bracket

Outlet	None
Packaging Type	Carton

This document was generated on Sep 14, 2025