

96FMCFI-2G-ET-AP4



- Sustained read: up to 20 MB/sec
- Sustained write: up to 11 MB/sec
- Advanced wear-leveling algorithms and Flash block management
- Built-in ECC
- Supports wide operation temperature: -40 ~ 85°C

Datasheet (PDF)

Get Quote

Product Specifications

Download Spec

Part Number	96FMCFI-2G-ET-AP4
Details	
Flash Card	
Manufacturer	APACER
Capacity	2 GB
Sequential Read Rate	29 MB/s
Sequential Writing Rate	15 MB/s
Operating Temperature	-40~ 85°C (-40 ~ 185°F)
NAND Type	SLC
DMA Mode	Ultra DMA
Disk Mode	Fixed Mode
Terabytes Written (TBW)	38.4

Support

Datasheet (PDF)

Documents & Downloads



Need more info? Talk to our Online Rep!

Live Chat

Inquiry Form

Related Materials

- All
- News (2)
- Catalog (1)

2018 Advantech Certificated Peripherals Catalog

【Phase Out】Apacer CFast 2A-M Series

【Phase In】Apacer CFast SM220

How Can We Help?



Support



Live Chat



1-888-576-9668



- [Company Information](#)
- [Investor Relations](#)
- [Contact Us](#)
- [Corporate Citizenship \(CSR\)](#)
- [Global Exhibitions](#)
- [Careers](#)