



## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	User manual
--------------------	-------------

## Physical

Cable length	0.91 m
Colour	Black
Depth	66 cm
Height	43.2 cm
Net weight	56.7 kg
Width	13 cm

## Input

Network frequency	50/60 Hz
Plug standard	NEMA L6-30P
Input voltage	208 V 240 V

## Output

Max current draw	5000 A
Number of power socket outlets	12
Number of power socket outlets	8 NEMA 5-20R 2 NEMA L6-20R 1 NEMA L6-30R 1 NEMA L14-30R
Output voltage	120 V 208 V

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Weight	63.5 kg
Package 1 Height	34.7 cm
Package 1 width	60.3 cm
Package 1 Length	98 cm
Number of Units in Package 3	6

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------