


THIS IS ISSUED IN STRICT CONFIDENCE
 THAT IT IS NOT USED AS A BASIS FOR
 MANUFACTURE OR SALE AND THAT IT
 IS NOT COPIED, REPRINTED OR
 DISCLOSED TO A THIRD PARTY EITHER
 WHOLLY OR IN PART WITHOUT THE
 PRIOR WRITTEN CONSENT OF CAL TEST
 ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/11/99	


- 4mm INSULATED BINDING POST, SOLDER TURRET
- SPECIFICATIONS:
 INSULATOR: POLYAMIDE (NYLON)
 JACK BODY: BRASS, NICKEL PLATED
 NUT: BRASS, NICKEL PLATED, 2 PIECES
- RATING:
 VOLTAGE: 1,200V AC/DC
 CURRENT: 36A MAX.
 TEMPERATURE: -20° C TO +80° C.
- MOUNTING HOLE: REFERENCE DIAGRAM.
- MAXIMUM PANEL THICKNESS: .20 (5.1)



PART NUMBER

CT2232-#

COLOR: 0 — BLACK
 2 — RED
 4 — YELLOW
 5 — GREEN
 6 — BLUE
 9 — WHITE



UNLESS OTHERWISE SPECIFIED
 DIMENSIONS ARE IN INCHES
 TOLERANCES ARE:
 FRACTIONS DECIMALS
 ± 1/32 .XX ± .02
 .XXX ± .005
 DO NOT SCALE DRAWING

CONTRACT NO.

APPROVALS

DRAWN WDH

CHECKED

ENGR.

DESIGN ACTIVITY

DATE

7/11/99

Cal Test Electronics

22820 Savi Ranch Parkway
 Yorba Linda, CA 92887-4610

TITLE

4mm INSULATED BINDING POST,
 SOLDER TURRET

SIZE

A

CAGE CODE

43F45

DWG. NO.

P223200

REV.

—

SCALE

1:1

SHEET

1 OF 1

NEXT ASSY

USED ON

APPLICATION