

2112DH2PG Product Details



2112DH2PG
(1423152-4)
TE Internal Number: 1423152-4

Active

Add to Part List

Time Delay Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- 2100 Miniature Timing Series
- Time Delay Relay
- Input Voltage = 48 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 120 VAC

View all Features

Find Similar Products

Quick Links

Check Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Request Samples

NEW!

Documentation & Additional Information	
Product Drawings: - None Available Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available	Additional Information: - Product Line Information Related Products: - Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Type = Time Delay Relay - Termination Type = 8-Pin Octal Style Plug Electrical Characteristics: - Input Voltage (VDC) = 48 - Contact Rating = 10A @ 120 VAC Body Related Features: - Series = 2100 Miniature Timing Contact Related Features: - Mounting Options = Chassis Mount - Mode of Operation = On-Delay - Delay Time = 2 seconds to 60 seconds - Type of Control = Screw - Repeatability, Max. = ± 5% @ 25°C, ± 7% @ 85°C, ± 8% @ 55°C - Approved Standards = CE Approved - Option = Hermetically Sealed - Approx. Dimensions (L x W x H) (mm [in]) = 63.50 x 38.60 x 123.90 [2.501 x 1.520 x 4.881]	Configuration Related Features: - Contact Arrangement = 2 Form C, DPDT, 2 C/O - Multiple Timing Ranges = Without Industry Standards: - RoHS/ELV Compliance = Not ELV/RoHS compliant - Lead Free Solder Processes = Not suitable for lead free processing Conditions for Usage: - Temperature Range (°C) = -55 – +85 Other: - Brand = Agastat