



Pushing Performance  
Since 1945

# M12 Power Fem PWR/PE Cont. Crimp 0,75mm²



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9932
Specification	M12 Power Fem PWR/PE Cont. Crimp 0,75mm²
HARTING eCatalogue	<a href="https://harting.com/21011009932">https://harting.com/21011009932</a>

## Identification

Category	Contacts
Series	Circular connectors M12
Identification	Power
Type of contact	Crimp contact
Description of the contact	23.2 mm length

## Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

## Technical characteristics

Conductor cross-section	0.75 mm²
Conductor cross-section [AWG]	AWG 20
Performance level	1

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



**Pushing Performance**  
 Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

## Specifications and approvals

PROFINET	Yes
----------	-----

## Commercial data

Packaging size	50
Net weight	0.32 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140229457
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors