




	1	2	3	4	5	6	7	8
A								
B								
C	25	33572110950001	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, AC	95				
	24	33572110850001		85				
	23	33572110750001		75				
	22	33572110700001		70				
	21	33572110660001		66				
	20	33572110550001		55				
	19	33572110520001		52				
D	18	33572110500002	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, AC	50				
	17	33572110420001		42				
	16	33572110400001		40				
	15	33572110300001		30				
	14	33572110200002	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, DC	20				
	13	33572110200001	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, AC	20				
	12	33572110180001		18				
	11	33572110150001		15				
E	10	33572110100002	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, DC	10				
	9	33572110100001	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, AC	10				
	8	33572110060002	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, DC	6				
	7	33572110050002		5				
	6	33572110050001	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, AC	5				
	5	33572110040001		4				
	4	33572110030002	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, DC	3				
	3	33572110020002		2				
	2	33572110010002		1				
F	1	33572110010001	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, AC	1				
	Cont. no.	Part no.	Type of cable	Dim a[m]				
	1	2	3	4	5	6	7	8

		All Dimensions in mm Original Size DIN A3		Scale 1:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by OLESCHR		Inspected by AVRAM		Standardisation HOFFMANN		Date 2013-05-20		State Final Release			
		Department EC PD - RO		Title Hybrid cable assembly								Doc-Key / ECM-Nr. 100154019/UGD/013/A 500000062191			
HARTING Electronics GmbH D-32339 Espelkamp				Type TB		Number 33572110XX000X						Rev. A		Page 2/2	