


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	REV PER ECN-22-156403	06JUN2022	RK	CSD



- 1 TONGUE MATERIAL THK IS $.027 \pm .001$
- 2 FOR .050 TO .105 WIRE INS. DIA.
- 3 MUST BE CRIMPED WITH 22-18 OR 22-16 PIDG (RED) TOOL.
- 4 MEETS MS25036-147, CLASS 1
- 5 NOTE DELETED

2500	ON TAPE, REEL	54312-2	BODY: COPPER ASTM B152 TIN PL PER ASTM B545 SLEEVE: COPPER ASTM B152 TIN PL PER ASTM B545 INSULATION: NYLON, COLOR: YELLOW
1000	LOOSE PIECE	 54312-1	
QTY	PACKAGE TYPE	PART NO	MATERIAL & FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 27JAN04	TE Connectivity						
		CHK T MICHIELUTTI 27JAN04							
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T MICHIELUTTI 27JAN04	NAME TERMINAL, NYLON PIDG, RING TONGUE; WIRE SIZE 26-24 —						
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .008 4 PLC ± — ANGLES ± 1°	PRODUCT SPEC —							
		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
	MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —	A3	00779	C-54312		—	
CUSTOMER DRAWING			SCALE		8:1	SHEET	1 OF 1	REV	C3