







P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-25-302515	17JAN2025	TR	RCG

Note:
X= 1,2,3,4,5,6
YYWWDD
YY=YEAR
WW=WEEK
D=1 for Sunday -
7 for Saturday


Marking



RECOMMENDED P.C.B LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.05)




LED PIN DEFINE



Recommended panel cutout

- NOTE :
- 1.Housing:Glass Filled PA46 BLACK.(RoHS)
 - 2.Shielding:C2680 T=0.20mm Nickel Plated MIN 30u".
 - 3.Contact:T0.35mm, Nickel Plated MIN 50".
 - 4.Insert:Glass Filled PBT BLACK.(RoHS)
 - 5.LED1:GREEN&ORANGE
 - ※MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68,SUBPART F.
 - ※ The dimension with ▲ marked is key dimension



GF	2497308-6
0.0762 μm [3 μ "]	2497308-5
0.1524 μm [6 μ "]	2497308-4
0.381 μm [15 μ "]	2497308-3
0.762 μm [30 μ "]	2497308-2
1.27 μm [50 μ "]	2497308-1
GOLD PLATING THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TARUN, R 21NOV2024		 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK RAMESH, KIVADER 22NOV2024					
		APVD RAGHAVAN, CG 22NOV2024		NAME RJ45 W/O MAGNET 1X4 1G LED — —			
		PRODUCT SPEC 108-161621					
		APPLICATION SPEC 114-161218					
		WEIGHT —					
		CUSTOMER DRAWING					
MATERIAL —		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C=2497308	RESTRICTED TO —
				SCALE 1:1	SHEET 1 of 1	REV A	