Specifications



Photo is representative





Eaton DR1040-221-R

Eaton DR1040 inductor, 216 uH, 0.7 A Irms, 0.92 A ISAT, 640 mΩ resistance, SMT mounting, Ferrite, 2-pins, 850 qty.

General specifications	
PRODUCT NAME	Eaton DR1040 inductor
CATALOG NUMBER	DR1040-221-R
UPC	051712829182
PRODUCT LENGTH/DEPTH	10.5 mm
PRODUCT HEIGHT	4 mm
PRODUCT WIDTH	10.3 mm
PRODUCT WEIGHT	1.79 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.7 A
ISAT	0.92 A
PACKAGE QUANTITY	850
MATERIAL	Ferrite
AUTOMOTIVE GRADE	No
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	640 mΩ
TERMINALS	10.0x10.0x4.0mm
SERIES	DR1040

Resources

SPECIFICATIONS AND DATASHEETS	Eaton DR1040 shielded power inductors data sheet Eaton Specification Sheet - DR1040-221-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.