



Part Number : [1300960044](#)
Product Description : Liquid-Tight Grip Strain Relief,
1/2" NPT, 45° Angle Male, Mesh Length 0.098m
(3.875")
Series Number : 130096
Status : Obsolete
Product Category : Cable Grips
Engineering Number : 36390



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130096
Description	Liquid-Tight Grip Strain Relief, 1/2" NPT, 45° Angle Male, Mesh Length 0.098m (3.875")
NEMA Rating	NEMA 4
Product Name	Liquid-Tight
Type	Strain Relief Grip
UPC	78678836390

Agency

CSA	LR32159
UL	E61303

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	45° Angle
Cable Diameter	N/A
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Malleable Iron, Zinc Plated Steel
Material - Grip	Stainless Steel
Mesh Length	0.098m (3.875")
Number of Holes	N/A
O-Ring	N/A
Thread Size	1/2" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>
MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black	<u>1300990149</u>
MAX-LOC O-Ring, 1/2" NPT	<u>1301800314</u>

This document was generated on Sep 11, 2025

Obsolete