

ASSMANN USB 2.0 connection cable

AK-300105-010-S
EAN 4016032283669



USB 2.0 connection cable, type A - B M/M, 1.0m, USB 2.0 conform, bl

For connection of external USB devices (with B socket, e. g. external HDD enclosure, scanner or printer) to the USB Host (e. g. PC, Notebook or USB Hub). Datatransferrate up to 480 Mbps (High-Speed).

Allows a reliable and fast connection of external USB devices with the PC, also about longer distances.

- Connector 1: USB A, plug
- Connector 2: USB B, plug
- USB compliance: USB 2.0

- Hoods: molded
- Shielding: Double shielding
- AWG: 28
- Wire material: CU
- Connector surface: nickel-plated
- Ferrite filter: none
- Color cable: black
- Color connector: black
- Length: 1 m
- Packaging: Polybag
- Assortment: USB Cables

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	250	10.90	45.00	32.00	25.00	36,000.00
Packaging Unit Inside	1	0.04	1.00	16.00	19.00	304.00
Packaging Unit Single	1	0.04	1.00	16.00	19.00	304.00
Net single without Packaging	1	0.00	1.00	14.00	13.00	182.00

USB 2.0

More images:

