

**Part Number :** [634451122](#)

**Product Description :** Anvil

**Series Number :** 207128

**Status :** Active

**Product Category :** Applicators and Crimp Modules



---

## Documents and Resources

### Tooling Specifications

[ATS-STANDARD-PARTS-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Applicators and Crimp Modules
Series	207128
Description	Anvil
Comments	See Tooling Specification (PDF) Above
Function	Cutter
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Applicator
UPC	800753155510
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

### Physical

Net Weight	1.000/g
------------	---------

## Mates With / Use With

### Use with Part(s)

Description	Part Number
FineAdjust Applicator	<u>638208000</u>
T2 Terminator Die	<u>638508000</u>
FineAdjust Applicator	<u>638608000</u>
FineAdjust Applicator for Insulation OD 0.63-1.10mm, 30-26 AWG	<u>639001600</u>
FineAdjust Applicator for Insulation OD 1.12-1.27mm, 30-26 AWG Wire	<u>639004400</u>
T2 Terminator for Insulation OD 1.12-1.27mm, 30-26 AWG	<u>639104400</u>

---

This document was generated on Apr 29, 2026