



REV.	DESCRIPTION	DATE	APPROVED
1	RELEASED PER E064258	01/25/06	MH



- NOTES:
1. FOR MATERIAL SPECIFICATIONS AND RESTRICTION ON HAZARDOUS SUBSTANCE (RoHS) REQUIREMENTS, CONFORMANCE TO CST-0001, LATEST REVISION.
 2. UL RECOGNIZED FILE E19180, GUIDE JDYX2; CSA CERTIFIED FILE 42731, CLASS 1421-01

ELECTRICAL SPECIFICATIONS

AMPERAGE	3 AMPS
VOLTAGE	250 VOLTS
INTERRUPTING & VOLTAGE RATINGS	50 AMPS
TIME- CURRENT CHARACTERISTICS	CARRY 100% FOR 4 HRS MIN. OPEN AT 200% IN 10 SEC MAX.
COLD RESISTANCE DATA	0.071 Ω

DRAWN BY <i>P.E.IENI</i>	DATE <i>08/02/05</i>			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES- TOLERANCES ARE: FRACTIONS DECIMALS ANGLES $\pm 1/64$.XX= $\pm .01$ $\pm 1^\circ$.XXX= $\pm .005$		FUSE 3A 250V LEADED		
THIRD ANGLE PROJECTION 	SIZE B	FSCM NO. 67131	DWG NO 30243	REV 1
DO NOT SCALE DRAWING	SCALE 2:1	SHEET 1 OF 1		