

 [Live Product Chat](#)



✓ Active

 [Add to Part List](#)

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Switch - Mechanical
- Not Tactile
- Single Pole - Double Throw Configuration (Pole-Throw)
- Contact Rating = 0.4VA
- Operating Function = Momentary

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

- None Available

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

- Product Type = Switch - Mechanical
- Tactile = No
- Configuration (Pole-Throw) = Single Pole - Double Throw
- Mount Angle = Right Angle
- Termination Type = Printed Circuit
- Actuator Style = Square

- Contact Rating = 0.4VA

- Series = TP
- Mount Style = Through-Hole
- Actuator Length (mm [in]) = 3.15 [0.124]
- Actuator Profile = Extended
- Actuator Color = Blue
- Case Material = Polyester
- Actuator Material = Polyamide

- Contact Plating = Gold over Nickel

- Process Sealed = No
- Low Profile = No

- Operating Function = Momentary
- Ganged = No
- ESD Grounding Terminal = Without
- Actuator Force (g [oz]) = 50.00 - 400.00
[1.770 - 14.120]
- Number of Actuators = Single
- Illuminated = No
- Dust Proof = No
- Support Bracket = Without
- Snap Action = Without

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Temperature Rating = High

- Packaging Method = Loose Piece

- Brand = Alcoswitch