
# Specification Sheet

Part Number: 553-50019



Slide Slit and optional center slits for easy wire insertion.

Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.

ShrinkTrak Labels, 1-Sided, 1-Slit, 0.25" (6.35mm), PO-X, White, 500/box

| | |
|---|---|
| Article Number | 553-50019 |
| Type | HST6-2WH-S |
| Color | White (WH) |
| Quantity Per | pack |
| Product Description | HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production. |
| Short Description | ShrinkTrak Labels, 1-Sided, 1-Slit, 0.25" (6.35mm), PO-X, White, 500/box |

Downloaded from Arrow.com.

| | |
|---|---|
| Global Part Name | HST6-2WH-S-PO-X-WH |
| Variant | Thin-Wall |
| Width W (Imperial) | 0.95 |
| Width W (Metric) | 24.13 |
| Thickness T (Imperial) | .003 |
| Thickness T (Metric) | .0762 |
| Height H (Imperial) | 0.42 |
| Height H (Metric) | 10.67 |
| Width of Liner (Metric) | 76.2 |
| Width of Liner (Imperial) | 3.0 |
| Outside Diameter OD (Imperial) | 0.25 |
| Outside Diameter OD (Metric) | 6.35 |
| Outside Diameter Max (Imperial) | 0.25 |
| Outside Diameter Max (Metric) | 6.35 |
| Wall Thickness WT (Imperial) | 0.028 |
| Wall Thickness WT (Metric) | 0.71 |

Downloaded from Arrow.com.

| | |
|---|---|
| Material | Polyolefin, cross-linked (PO-X) |
| Material Shortcut | PO-X |
| US MIL SPEC | SAE-AS81531<br>SAE-AMS-DTL-23053/5 Class 1 and 3<br>MIL-STD-202G Method 215K |
| Flammability | UL 224 VW-1 |
| Halogen Free | No |
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor Use Only |
| Operating Temperature | -67°F to +275°F (-55°C to +135°C) |
| BABA Compliant | YES |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | SAE - AMS - DTL-23053/5 Class 1 and 3 SAE - AS81531 UL 224 125 °C 600V VW-1 |
| Package Quantity (Imperial) | 500 |
| Package Quantity (Metric) | 500 |

Downloaded from Arrow.com.

| | |
|---|---|
| Customs Number | 3917320000 |
| Labels per Column | 1 |
| Labels per Row | 2 |

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.



Downloaded from Arrow.com.