



PCB layout

Specifications:

Current Rating: 1.5A AC/DC

Voltage Rating: 30V AC/DC

Contact Resistance: 20m Ohm. Max.

Insulation Resistance: 1000M Ohm. Min.

Withstanding Voltage: 750V AC/Minute

Operating Temperature Range: -40°C ~ +105°C

Materials:

Insulator: LCP(UL94V-0)

Insulator Color: White



Contact: Brass


Plating: Gold Flash Plated in Contact Area,
Tin Plated on Solder Tails.

△ Shell: Brass, Nickel Plated




RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology	
				CHECKED:	UNIT: MM	DESCRIPTION: USB A Male SMD Type,G/F	SIZE A4
					SCALE:1:1		
				APPROVAL:	SHEET: 1 / 2	PART NO: 1001-011-01101-TR	
					PROJECTION: 		
REV	DATE	FILE	BY				






PULL OUT DIRECTION




Note:

- 1.Material : Black Conductive Polystyrene Alloy
100% recyclable.
- 2.Thickness : 0.35±0.05mm
- 3.Component load per 13" reel :500 Pcs.
- 4.Carton Size:350*350*296(mm)



Pin No	W	PCS/R	R/CTN	Q'TY
04	44	500	5	2500

				04		44		500		5		2500		RoHS Compliant	
				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology						D			
				CHECKED:	UNIT: MM	DESCRIPTION: USB A Male SMD Type,G/F						SIZE A4			
					SCALE:1:1										
				APPROVAL:	SHEET: 2 / 2	PART NO: 1001-011-01101-TR									
					PROJECTION:										
REV	DATE	FILE	BY												