Part Number : 191890004
Product Description : Krimptite Butt Splice for 22-18 AWG Wire
Series Number : 19189
Status : Active
Product Category : Splices
Engineering Part Number : A-145T



Documents and Resources

Drawings

191890004_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19189
Description	Krimptite Butt Splice for 22-18 AWG Wire
Product Name	Krimptite
Style	Standard
Type	Butt Splice
UPC	800753037755

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.702/g
Packaging Type	Adhesive Tape on Reel
Wire Size (AWG)	18, 20, 22

Downloaded from Arrow.com.

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	638854500

This document was generated on Apr 11, 2026

Downloaded from Arrow.com.