



**GARDTEC**

Part Number:

## **HP100** ("Straight" Plug)

Wire: **SPT1 2 and 3 conductor 105°C, 300 volts**

Lengths: **Standard** (12", 24", 36", 40",  
48", 50", 60" and 80")


**Custom** (any length you desire.


When ordering, add desired length to  
part number (i.e. 52.5" would be HP100-52.5))

Other options:

- **terminal connections** (any)
- **heat shrink**
- **labeling**
- **stripping**
- **tinning**
- **three conductor cords**
- **complete wire harness assemblies**  
(rated at 105°C, 300 volts)
- **red tracer cords**  
(all head configurations and lengths)

Listings:

 **UL listed** (E189621, E156798)  
Rated 10 AMP/125 VAC

 **CSA listed** (LR76679-1)  
Rated 7 AMP/125 VAC

