

Power Extension Cord, C19 to Right Angle C20 - Heavy Duty, 20A, 250V, 12 AWG, 2 ft., Black

MODEL NUMBER: P036-002-20RA



Heavy-duty extension cable with right-angle C20 end allows connection of C19/C20 high-output devices in tight spaces or awkward angles.

Features

**20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection**This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The two-foot length helps reduce cable clutter and minimize the risk of tripping.

**Right-Angle C20 Plug Makes Connecting in Tight Spaces Easier**The C19 to C20 right-angle cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled C20 plug guides the heavy-duty extension cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

Highlights

- Right-angle C20 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering servers, routers and other high-output network devices
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 2 ft. away in your data center
- Extend an existing power connection up to 2 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

Package Includes

- P036-002-20RA C19 to Right-Angle C20 Heavy-Duty Extension Cord, 2 ft., Black

Specifications

| OVERVIEW                    |               |
|-----------------------------|---------------|
| UPC Code                    | 037332156532  |
| Country/Region              | North America |
| INPUT                       |               |
| Maximum Input Amps          | 20            |
| Voltage Compatibility (VAC) | 100-250       |
| PHYSICAL                    |               |

|                                      |                           |
|--------------------------------------|---------------------------|
| Color                                | Black                     |
| Power Cord Jacket Type               | SJT                       |
| Number of Conductors                 | 3                         |
| Wire Gauge (AWG)                     | 12                        |
| Wire Gauge (OD - mm <sup>2</sup> )   | 3.31                      |
| Cable Length (ft.)                   | 2                         |
| Cable Length (m)                     | 0.61                      |
| Shipping Dimensions (hwd / in.)      | 0.50 x 5.00 x 7.60        |
| Shipping Dimensions (hwd / cm)       | 1.27 x 12.70 x 19.30      |
| Shipping Weight (lbs.)               | 0.50                      |
| Shipping Weight (kg)                 | 0.23                      |
| <b>CONNECTIONS</b>                   |                           |
| Side A - Connector 1                 | IEC-320-C20 - RIGHT ANGLE |
| Side B - Connector 1                 | IEC-320-C19               |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| High Voltage                         | Yes                       |
| Locking Plug                         | No                        |
| <b>WARRANTY &amp; SUPPORT</b>        |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |