

Current refinements (click  to remove) Search Tips

 Region  USA  Product Family  HSTT Heat Shrink 4 ft. Pieces and Reels  Text Search: 'HSTT75-48-545'

Your search criteria matched only one product, shown below.



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance

For clear, add "C" to end of part number package suffix (Example HSTT0548-QC). Contact customer service for additional color information.

Meets Mil Spec AMSDTL-23053/5 Class 1(Colors), Class 2 (Clear)

Part Number:	HSTT7548-545
RoHS Compliancy Status:	Compliant
Part Description:	Thin Wall Polyolefin Heat Shrink
Material:	Flame retardant polyolefin cross-linked except clear
Color:	Yellow/Green
CSA Certified:	Yes
Military Specification:	AMS-DTL-23053/5 Class 1
UL Recognized:	E122770
Length (ft.):	4
Length (m):	1.2
Flammability Rating:	Flame Retardant
Max. Recovered I.D. (In.):	.375
Max. Recovered I.D. (mm):	9.5
Min. Expanded I.D. (In.):	.750
Min. Expanded I.D. (mm):	19.0
Nominal Diameter / Size:	.750
Nominal Recovered Wall Thickness (In.):	.030
Nominal Recovered Wall Thickness (mm):	.8
Shrink Ratio:	2:1
Temperature Range:	-67°F to 275°F (-55°C to 135°C)
Min. Order UOM:	PC
Min. Order Qty.:	5
BOM Qty. (# of Pkgs.)	0

Add to My Catalog 

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.