





REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
F		UPDATE FRAME	Staven 2020-11-13	Staven 2020-11-13	Biao 2020-11-13
G	ECN2022112	UPDATE CPK SYMBOLS	Abner 2022-07-20	Staven 2022-07-20	Sam 2022-07-20




NOTES:


- 1、MATERIAL: SUS 304-H T=0.15mm;
- 2、ALLOW BURR 0.03mm Max.;
- 3、PLATING: Au 2u" SURFACE PLATING OVER CONTACT AREAS,
Au 2u" SURFACE PLATING OVER SOLDER AREAS,
Ni 40-120u" UNDER PLATING OVER ALL.
- 4、"▼"THE SYMBOL IS REPRESENTED AS CPK AND $\bar{X}$ -R.

TABLE:

PART NUMBER	A	B	C	D
Z00D-4G7L1-11000	$4.8^{+0.3}_{-0.05}$	$1.5^{+0.0}_{-0.3}$	1.50	$3.90^{+0}_{-0.20}$
Z007-4G7L1-11000	$5.2^{+0.3}_{-0.05}$	$1.9^{+0.0}_{-0.3}$	1.05	$3.90^{+0}_{-0.20}$
Z00C-4G7L1-11000	$7.5^{+0.3}_{-0.05}$	$4.2^{+0.0}_{-0.3}$	1.50	$3.90^{+0}_{-0.20}$
Z00F-4G7L1-11000	$9.0^{+0.3}_{-0.05}$	$5.7^{+0.0}_{-0.3}$	0.80	$3.90^{+0}_{-0.5}$
Z00N-4G7L1-11000	$6.3^{+0.3}_{-0}$	$3.0^{+0.15}_{-0}$	1.50	$3.90^{+0.15}_{-0}$
Z00E-4G7L1-11000	$4.0^{+0.3}_{-0}$	$0.7^{+0.15}_{-0}$	1.50	$3.90^{+0.15}_{-0}$
Z00X-4G7L1-11000-E000	$5.6^{+0.3}_{-0}$	$2.3^{+0.15}_{-0}$	1.50	$3.90^{+0.15}_{-0}$

UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION 		 Amphenol Aorora Technology (Huizhou) Co.,Ltd			
X.	±0.30	X. *	± 5'			TITLE: SPRING			
X.X	±0.25	X.X *	± 4'						
X.XX	±0.20	X.XX *	± 3'						
X.XXX	±0.15	X.XXX *	± 2'	DOC TYP		Customer Drw			
LINEAR DIMS		ANGLES DIMS		DRAWN		DATE		Abner 2022-07-20	
DWG NO.: A-S0198				DESIGN		DATE		Abner 2022-07-20	
MATERIAL		SEE NOTES		CHECKED		DATE		Staven 2022-07-20	
FINISHED		SEE NOTES		APPROVED		DATE		Sam 2022-07-20	
SIZE		PART NUMBER:		SCALE		1:1		UNIT : mm	
SHEET		1 OF 1		REV.		G		SEE TABLE	

1:PACKING INTO REEL



NOTES:


- MATERIAL:
 - CARRY TAPE: HIPS, T=0.50mm, CLEAR
 - REEL: HIPS, BLUE.
 - SHIM: PE, CLEAR.
- PRIMARY PACKING: 900PCS/REEL.
- SECONDARY PACKING: 10 REELS/CARTON
("TOTAL"=10*900/CARTON).
- PEELING RESISTANCE: 0.1N~0.7N(10~70gf);
PEELING ANGLE: 165°~180°;
PEELING SPEED: 300mm/minutes.


REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
D	ECN2022112	UPDATE FRAME	Abner 2022-07-20	Staven 2022-07-20	Sam 2022-07-20

TABLE:

PART NO.	PCS/REEL	N REEL/BOX (TOL PCS)
Z007-4G7L1-11000	900	10REEL/BOX (9000pcs)
Z01P-4G7L1-11000-E000		

2:PACKING INTO OUTER BOX



UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION 		 Amphenol Aorora Technology (Huizhou) Co.,Ltd										
X.	±0.15	X. °	± 1'	DOC TYP	PACKING DWG.		TITLE: SPRING H5.2									
X.X	±0.10	X.X °	± 0.5'													
X.XX	±0.05	X.XX °	± 0.5'													
X.XXX	±0.03	X.XXX °	± 1'													
LINEAR DIMS		ANGLES DIMS														
DWG NO.: A-H0108				DRAWN		DATE	Abner	SIZE A4		PART NUMBER: SEE TABLE		REV. D				
MATERIAL		SEE NOTES		DESIGN		DATE	Abner									
				CHECKED		DATE	Staven									
				APPROVED		DATE	Sam									
				FINISHED		SEE NOTES										
						2022-07-20	SCALE						1:1	UNIT : mm	SHEET 1	OF 1