


CONFIGURATION	PART NUMBER	LENGTH
MINI, 3 PIN, 16AWG MALE INLINE STRAIGHT FEMALE PLUG STRAIGHT	MN37A4AC01Mxxx	AS REQUESTED

DIMENSIONS



TECHNICAL DATA

APPROVALS:	UL, c(UL)
TEMPERATURE RANGE:	-20C to +105C
PROTECTION:	IP 67, NEMA 6P
VOLTAGE RATING:	600VAC
AMPERAGE:	13A
HOUSING:	OIL RESISTANT PVC
CONTACTS:	COPPER ALLOY
CONTACT PLATING:	GOLD OVER NICKEL PLATING
CONNECTOR FACE:	PVC
COUPLING:	MACHINED ALUMINUM, ANODIZED
CABLE CHARACTERISTICS:	STOOW 600V 105°C CSA ST FT2-ROHS PVC INSULATED 16AWG STRANDED COPPER (65x #34)

Sales and Technical Support 1-800-394-7732

www.sineco.com

Amphenol
SINE SYSTEMS

© 2011 Amphenol Sine Systems Corporation. Every effort has been made to ensure that the information contained in this document is accurate at the time of publication. Specifications or information stated in this publication are subject to change without notice.