




1		2		3		4											
																	
<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~04*1TV~</td><td>WHITE</td></tr><tr><td>~04*2TV~</td><td>BLACK</td></tr></tbody></table>								Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK				
Part No.	Cable color																
~04*1TV~	WHITE																
~04*2TV~	BLACK																
NOTE 1 We indicate the length of the harness on the last of product name, 'L' part. 2 Tolerance for [L] <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>$35 \leq L \leq 200$</td><td>± 4</td></tr><tr><td>$200 < L \leq 500$</td><td>± 8</td></tr><tr><td>$500 < L \leq 1000$</td><td>± 12</td></tr><tr><td>$1000 < L$</td><td>$\pm 1.5\%$</td></tr></tbody></table> 3 Connector rotation angle is within ± 45 degree from the above image. For long length in the case of $L > 500$, the angle is optional. 4. Specifications are subject to change without notice. 【 DIMENSIONS OF CONNECTOR 】 								Length L [mm]	Tolerance [mm]	$35 \leq L \leq 200$	± 4	$200 < L \leq 500$	± 8	$500 < L \leq 1000$	± 12	$1000 < L$	$\pm 1.5\%$
Length L [mm]	Tolerance [mm]																
$35 \leq L \leq 200$	± 4																
$200 < L \leq 500$	± 8																
$500 < L \leq 1000$	± 12																
$1000 < L$	$\pm 1.5\%$																
1 U.FL-LP-040HF		CL331-0557-3		2 0.81 Dia. coaxial cable		HALOGEN FREE											
NO. PART NO.		CODE NO.		NO. PART NO.													
UNITS mm		SCALE FREE		COUNT		DESCRIPTION OF REVISIONS											
						DESIGNED											
F		APPROVED : TS. NOBE		18.06.18		DRAWING NO.											
		CHECKED : MT. KANEKO		18.06.18		PART NO. U.FL-2LPHF6-04**TV-A-L 1											
HIROSE ELECTRIC CO., LTD.		DESIGNED : MS. MATSUMOTO		18.06.18		CODE NO.											
		DRAWN : MS. MATSUMOTO		18.06.18													
FORM HC0011-5-51		2		3		4											