



+ CONNECTORS
RF CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
F Type Blk Jk R/M 75 Ohm RG6/U
MICRO MIN SURFACE MOUNT COAX | BBK , G Series

5-1814826-3
TE Internal Number: 5-1814826-3

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Connector Interface F Series

Connector Style Jack

Impedance (Ω) 75

Cable Type RG 6

Sealable No

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

F TYPE BLK JK R/M

PDF

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

Economy RF Coaxial Connectors

TIF

English

Economy RF Coaxial Connectors

PDF

English

Qualification Test Report

Economy ZDC RF Coaxial Connector Qualification Test Report

TIF

English

Economy ZDC RF Coaxial Connector Qualification Test Report

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface F Series

Connector Style Jack

Sealable No

Connector & Contact Terminates To Wire & Cable

Electrical Characteristics

Impedance (Ω) 75

Body Features

Body Material Brass

Body Plating Material Nickel

Contact Features

Center Contact Plating Material Tin

Center Contact Material Brass

Termination Features

Termination Method to Wire & Cable Crimp

Mechanical Attachment

Panel Attachment Style Rear

Usage Conditions

Cable Type RG 6

Packaging Features

Packaging Method Box

Other

Dielectric Material Polypropylene

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF