
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✔ Active

TE CONNECTIVITY (TE)

070 MLC PLUG 18P HSG

Multilock Connector System

368544-1
TE Internal Number: 368544-1

EU RoHS Compliant
EU ELV Compliant

Mating Tab Width 1.8 mm [.071 in]
Connector System Wire-to-Wire
Number of Positions 18
Sealable No
Hybrid Connector No

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

070 MLC 18P PLUG HSG
PDF
English

CAD Files

Customer View Model
2D_DXF.ZIP
English

3D PDF
PDF
3D

Downloaded from Arrow.com.

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Agency Approvals

UL Report

.070 SERIES MULTI-LOK I/O CONNECTOR REPORT

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Wire
Sealable No
Hybrid Connector No
Strain Relief No
Row-to-Row Spacing 5.9 mm [.232 in]

Configuration Features

Number of Positions 18
Number of Rows 2

Body Features

Color White
Body Material PBT GF

Contact Features

Mating Tab Width 1.8 mm [.071 in]

Mechanical Attachment

Mounting Feature No
Terminal Position Assurance No
Polarized Yes

Dimensions

Width 25.5 mm [1.0039 in]
Height 21.6 mm [.85 in]
Length 42.3 mm [1.665 in]

Downloaded from Arrow.com.

Operation/Application

Circuit Application Signal

Packaging Features

Packaging Method Bag
Packaging Quantity 150

Other

Connector Position Assurance Capable No

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.