



**Part Number :** 192030183

**Product Description :** VersaKrimp Temp-Term Butt Splice for 12-10 AWG Wire, 343°C (650° F), Loose Piece

**Series Number :** 19203

**Status :** Active

**Product Category :** Splices

**Engineering Number :** C-T-346



## Documents & Resources

### Drawings

[192030183\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-19902-013-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## **Part Details**

### **General**

Status	Active
Category	Splices
Series	19203
Description	VersaKrimp Temp-Term Butt Splice for 12-10 AWG Wire, 343°C (650° F), Loose Piece
Product Name	VersaKrimp
Style	High Temperature
Type	Butt Splice
UPC	800755060096

### **Physical**

Barrel Type	Closed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel
Net Weight	2.456/g
Packaging Type	Carton
Temperature Range - Operating	343°C
Wire Insulation Diameter	5.80mm
Wire Size (AWG)	10, 12

## **Solder Process Data**

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup>	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

---

This document was generated on Sep 25, 2025