

# Pushbutton, 16.2 mm, momentary contact function, 1 NO, bezel black



**Description**

Pushbutton with mounting hole diameter 16.2 mm, screw terminal, non-illuminated

## technical data

> **general**

|                                                             |                                       |
|-------------------------------------------------------------|---------------------------------------|
| Bezel color                                                 | black                                 |
| Property of bezel / mushroom                                | opaque                                |
| Collar shape                                                | round                                 |
| Operating temperature, min.                                 | -25 °C                                |
| Operating temperature, max.                                 | 85 °C                                 |
| Storage temperature, min.                                   | -40 °C                                |
| Storage temperature, max.                                   | 90 °C                                 |
| illuminated                                                 | No                                    |
| Packaging                                                   | Box                                   |
| Packaging unit                                              | 100 pcs.                              |
| Net weight                                                  | 11 g                                  |
| Operating life                                              | 150,000 cycles                        |
| B10                                                         | 195,000 cycles                        |
| Degree of protection, front side, according to DIN EN 60529 | IP40<br>IP65<br>IP65 with sealing cap |
| Minimum order quantity (MOQ)                                | 100 pcs.                              |
| RoHS compliant                                              | Yes                                   |
| REACH compliant                                             | Yes                                   |
| Country of origin                                           | HU                                    |

> **mounting diameters**

|                           |         |
|---------------------------|---------|
| Outside dimension, length | 20 mm   |
| Outside dimension, width  | 20 mm   |
| Outside dimension, height | 50 mm   |
| Mounting hole             | 16.2 mm |
| Mounting depth            | 41 mm   |
| Installation height       | 9 mm    |

> **mechanical data**

|                      |                            |
|----------------------|----------------------------|
| Terminal on the rear | Screw terminal             |
| Fixing               | Threaded ring              |
| Actuation function   | momentary contact function |

**direct links**

> [RAFI eCatalog](#)

|                        |                |
|------------------------|----------------|
| Operating force, min.  | 7,5 N          |
| Operating travel, max. | 4.3 mm         |
| Contact function       | 1 NO           |
| Contact system         | Bridge contact |
| Contact material       | Silver         |

> **electrical data**

|                     |       |
|---------------------|-------|
| Rated voltage, max. | 250 V |
| Rated current, max. | 2 A   |

## drawings

### Dimensioned drawing

