

Product Line

- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >



SC-L-PG13-05-YW

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: CSA, UL2238, UL50e

You must login first for view the price

Quantity


-1+

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Specifications		Download / CAD	
Nominal Current 8A		Connector Type Field Installable	
Shielded Plastic, Non-shielded		No. of Contacts 05	
Connector Gender N/A		Backshell N/A	
Mating Style Screw Thread		IP Rating IP69K	
PORT		PARTNERS	
Assembly Style Screw-in		DOWNLOAD CENTER	
		FEEDBACK	
<div> More Options</div>			

People Also Bought



ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

FICX PG11

FICX PG12

FICX PG13

FICX PGT2

FICX UL11

FICX UL12

FICX UL13

FICX ULT2

M20

M32

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >