



Part Number : [1300900019](#)
Product Description : Woodhead Standard Cord Reel, 16/3 SJTOW Cord, 10.67m (35.0') Cord Length with 15A Pendant Outlet Box, Two Duplex, NEMA 5-15 Outlets
Series Number : 130090
Status : Active
Product Category : Electrical Reels
Engineering Number : 966



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Electrical Reels
Series	130090
Description	Woodhead Standard Cord Reel, 16/3 SJTOW Cord, 10.67m (35.0') Cord Length with 15A Pendant Outlet Box, Two Duplex, NEMA 5-15 Outlets
Comments	Ratchet Lock (ON/OFF Switchable); (2) NEMA 5-15 Duplex Receptacles
Enclosure Rating	NEMA 1
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678875261

Agency

UL	E22769
----	--------

Electrical

Current - Maximum per Contact	6.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V

Physical

Bulb Included	N/A
Cable Length	0.457m (1.50')
Cable Movement	Ratchet Lock
Cord Length	10.67m (35.0')
Cord Type	16/3 SJTOW
Depth	0.24m (9.59")
Drum Lock	Ratchet

Duty	Standard
Height	0.32 (12.62")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Steel
Mounting Style	Swinging
Net Weight	1.000/g
Number of Conductors	3
Number of Receptacles	4
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	0.9kg (2.0 lb)
Width	13.06mm (5.160")
Wire Size (AWG)	16

This document was generated on Sep 11, 2025