



Part Number : [1731120333](#)

Product Description : FCT Screw Lock with Cross Slit Head, #4-40 Thread, Nickel-plated Steel

Series Number : 173112

Status : Active

Product Category : D-Sub Accessories

Engineering Number : FVS1/5-K1163

Documents & Resources

Drawings


[Drawing 1731120333_sd.pdf](#)

Specifications

[Packaging Specification 1731120003-PK-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Accessories
Series	173112
Description	FCT Screw Lock with Cross Slit Head, #4-40 Thread, Nickel-plated Steel
IP Rating	N/A
Magnetic	Yes
Product Family	FCT D-Sub Connectors
Product Name	FCT Products
Type	Hood
UPC	191128070058

Physical

Accessory Type	Locking Mechanism
Material - Body	Steel
Net Weight	0.900/g
Packaging Type	Bag
Thread Size	4-40 UNC
Thread Type	Standard

This document was generated on Jul 28, 2024