

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size**
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



BD-05RMFS-QC8001

Operating Temperature: -40°C ~ +105°C
 Transmission Speed: N/A
 Shielded: Plastic, Non-shielded
 Jacket Material: N/A
 Certificate: UL2238, UL50e

You must login first for view the price

Quantity

Can't find? [Customize your part](#)

Mating Pair & Accessories

X-Lok, Standard... AB-BD05BL-BDBL -20°C ~ +80°C	X-Lok, Standard... AB-BD05BL-BDBL -20°C ~ +80°C	X-Lok, Standard... AB-BD05BL-BDBL -20°C ~ +80°C	X-Lok, Standard... AB-BD05BL-BDBL -20°C ~ +80°C	X-Lok, Standard... AB-BD05BL-BDBL -20°C ~ +80°C	X-Lok, Standard... AB-BD05BL-BDBL -20°C ~ +80°C
<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

Specifications	Download / CAD
Nominal Current 5A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 05
Connector Gender Male	Backshell Circular
Mating Style Push Lock	IP Rating IP68
Assembly Style Solder	

[More Options](#)

People Also Bought

