

3 Row Crimp Removable Cable Connector without Mounting Ears (PLUG)

RM33, Crimp Removable, Straight Plug, without Mounting Ears, 3-Row, Sizes: 11-080 | R Series

A family of male cable connectors that have three rows of contacts spaced at 0.075". These connectors come with crimp removable wire termination. They are available in sizes ranging from 11 to 80 contacts.

DOCUMENTS SPECIFICATIONS ADDITIONAL INFO

- Dimensional Information »
- Part Number Buildup »
- Fortron Discoloration »
- Contact Spring Plating »
- Hardware Information (Guide Sets) »
- View More »

PRODUCT MATES WITH

Image Coming Soon — 3 Row Crimp Removable Cable Connector with Mounting Ears (RECEPTACLE) »

Image Coming Soon — 3 Row Crimp Removable Cable Connector without Mounting Ears (RECEPTACLE) »

Image Coming Soon — 3 Row Crimped Wire Cable Connector with Mounting Ears (RECEPTACLE) »

Image Coming Soon — 3 Row Crimped Wire Cable Connector without Mounting Ears (RECEPTACLE) »

VIEW MORE »

3D Part Viewer (BUILD A PART NUMBER BELOW TO VIEW)

Reset

Build a Part Number

RM	3	3	2	-	023	-	18	1	-	59	00	-	
1 SERIES DESIGNATOR	2 BODY ROWS	3 BODY STYLE	4 BODY MATERIAL		5 SIZE		6 CONTACT TYPES	7 CONTACT PLATING		8 HARDWARE STYLE	9 POLARIZATION		10 OPTIONS

Downloaded from Arrow.com.

TO BEGIN: SELECT COMPONENTS

1 SERIES DESIGNATOR
- (•) RM - .075" Screw Machine PC Connector

2 BODY ROWS
- (•) 3 - Row

3 BODY STYLE
- (•) 3 - Plug, Straight, Without Mounting Ears

4 BODY MATERIAL
- (•) 2 - Polyphenylene Sulfide (PPS)

5 SIZE
- ( ) 11 Contacts
- (•) 23 Contacts
- ( ) 35 Contacts
- ( ) 47 Contacts
- ( ) 59 Contacts
- ( ) 71 Contacts
- ( ) 80 Contacts

6 CONTACT TYPES
- ( ) 00 - Contacts Not Supplied
- ( ) 17 - Pin, Straight, Crimp Removable (20-22 AWG)
- (•) 18 - Pin, Straight, Crimp Removable (24-26 AWG)
- ( ) 19 - Pin, Straight, Crimp Removable (28-30 AWG)

7 CONTACT PLATING
- ( ) 0 - No Plating
- (•) 1 - Gold Plated Termination

8 HARDWARE STYLE
- 59 - Hex Turning Jackset, .200"

To take action, please complete the steps to the left.

NEXT STEPS: TAKE ACTION

Part #: RM332-023-181-5900

Miltary #: n/a

- [ ] Quote
- [ ] Mechanical Model & Drawing
- [ ] Product Sample

REQUEST NOW

OUT OF STOCK

Find a Sales Rep

Looking to talk with a salesperson? Find your local representative here:

LOCATIONS CONTACT US

Customize Your Solution

AirBorn will work with you to design and build a product to your specifications.

LEARN MORE

Downloaded from Arrow.com.

9 POLARIZATION 00 - None (Polarization is not required or polarized h

10 OPTIONS (OPTIONAL)

3D

You have successfully built a valid part number:
You may now edit your com
part mates below.

Cookies Policy

This site uses cookies. By clicking "Accept," you agree to the storing of cookies on your device to enhance site navigation, analyze site usage, and assist in our marketing efforts.

Accept Decline

© 2018 AirBorn, Inc. All Rights Reserved.
100% Employee Owned
ISO9001 and AS9100 Certified

Downloaded from Arrow.com.