



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	08MAY2020	GK	DB

LABEL AND LINER DESIGN



PRESENTATION



OUTSIDE WOUND (BACK SLIT CENTRED)
LABEL ACROSS: 1
PER ROLL QTY: 30.48m / 100 feet

All dimensions in mm [Inch]

TE PN: 815438-000

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12MAY2020 CHK GOPALAKRISHNA HV 12MAY2020		 TE Connectivity			
LABEL HEIGHT:	±0.3 [.012]	DIMENSIONS: mm [INCHES] 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	D.BURGAT 12MAY2020		NAME TEDLAR® LABEL – YELLOW – CONTINUOUS 25.4mm x 30.4m (1inch x 100ft) —			
LABEL WIDTH:	±0.3 [.012]			APVD 12MAY2020 D.BURGAT					
WEB WIDTH:	±0.8 [.031]			PRODUCT SPEC TTDS-005					
VERTICAL REPEAT:	±0.8 [.031]*			APPLICATION SPEC —					
HORIZONTAL REPEAT:	±0.8 [.031]*			—					
PRINT POSITIONING:	±0.8 [.031]*	MATERIAL SEE TABLE	FINISH GLOSS	WEIGHT 106g		SIZE A2	CAGE CODE FB1U7	DRAWING NO C-TTVF100YW-100	RESTRICTED TO —
LEFT MARGIN:	±0.4 [.016]			CUSTOMER DRAWING		SCALE NTS	SHEET 1 of 1	REV A	
QUANTITY:	—0 % +2 %								
*NON ACCUMULATING									