
We connect and protect

Front Panel, Unshielded, 6 U, 8 HP, 2.5 mm, Al, Front Anodized, Rear Conductive

CATALOG NUMBER

30838-128





Front panel, unshielded, front anodized and rear conductive.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- Partial width front panel, Al, 2.5 mm
- Al, front anodized, conductive

PRODUCT ATTRIBUTES

- Rack Height: 6U
- Package Quantity: 1
- Accessory Type: Front panel
- Mounting: Screw-on Front
- Front Finish: Anodized


Downloaded from Arrow.com.

Rear Finish: Conductive
Treated Edges: No
Complies With: IEC 60297-3-101; IEEE 1101.1/10
EMC Shielding: No
Finish: Anodized; Passivated
Material: Aluminum
Product Type: Front Panel
Type: Front Panel without Handle
Net Weight: 0.07kg

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Downloaded from Arrow.com.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

Downloaded from Arrow.com.