


1		2		3		4		5		6		7		8				
A																		
	49	09473636044	RJl Ethernet Stranded Cable, 4xAWG 22/7, PVC, Cat. 5+, green				100	RJl Ethernet Stranded Cable, 4xAWG 22/7, PVC outdoor, Cat. 5+, black				100						
	48	09473636043					90					90						
	47	09473636042					80					80						
B	46	09473636041					70					70	92	09473636087	90	90		
	45	09473636040					60					60	91	09473636086	80	80		
	44	09473636039					50					50	90	09473636085	70	70		
	43	09473636038					40					40	89	09473636084	60	60		
C	42	09473636037					30					30	88	09473636083	50	50		
	41	09473636036					20					20	87	09473636082	40	40		
	40	09473636035					15					15	86	09473636081	30	30		
	39	09473636034					10					10	85	09473636080	20	20		
D	38	09473636033					9					9	84	09473636079	15	15		
	37	09473636032					8					8	83	09473636078	10	10		
	36	09473636031					7					7	82	09473636077	9	9		
	35	09473636030					6					6	81	09473636076	8	8		
E	34	09473636029					5					5	80	09473636075	7	7		
	33	09473636028					4					4	79	09473636074	6	6		
	32	09473636027					3					3	78	09473636073	5	5		
	31	09473636026					2					2	77	09473636072	4	4		
F	30	09473636025					1.5					1.5	76	09473636071	3	3		
	29	09473636024					1					1	75	09473636070	2	2		
	28	09473636023					0.5					0.5	74	09473636069	1.5	1.5		
	27	09473636022					100					100	73	09473636068	1	1		
A	26	09473636021					90					90	72	09473636067	0.5	0.5		
	25	09473636093					85					85	71	09473636066	100	100		
	24	09473636020					80					80	70	09473636065	90	90		
	23	09473636019					70					70	69	09473636064	80	80		
B	22	09473636092					65					65	68	09473636063	70	70		
	21	09473636018					60					60	67	09473636062	60	60		
	20	09473636091					55					55	66	09473636061	50	50		
	19	09473636017					50					50	65	09473636060	40	40		
C	18	09473636016					40					40	64	09473636059	30	30		
	17	09473636090					35					35	63	09473636058	20	20		
	16	09473636015					30					30	62	09473636057	15	15		
	15	09473636089					25					25	61	09473636056	10	10		
D	14	09473636014					20					20	60	09473636055	9	9		
	13	09473636013					15					15	59	09473636054	8	8		
	12	09473636012					10					10	58	09473636053	7	7		
	11	09473636011	9	9	57	09473636052	6	6										
E	10	09473636010	8	8	56	09473636051	5	5										
	9	09473636009	7	7	55	09473636050	4	4										
	8	09473636008	6	6	54	09473636049	3	3										
	7	09473636007	5	5	53	09473636048	2	2										
F	6	09473636006	4	4	52	09473636047	1.5	1.5										
	5	09473636005	3	3	51	09473636046	1	1										
	4	09473636004	2	2	50	09473636045	0.5	0.5										
	3	09473636003	1.5	1.5	Cont. no.	Part no.	Type of cable	Dim. a[m]										
A	2	09473636002	1	1	 All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing							
	1	09473636001	0.5	0.5	 All rights reserved Department HCS - RO		Created by BANCUD Banciu		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean		Date 2019-08-08		State Final Release			
	Cont. no.		Part no.		HARTING Customised Solutions D-32339 Espelkamp		Title HARTING PushPull RJ45 Cable Assembly		Type TB		Number 09473636XXX		Doc-Key / ECM-Nr. 100155480/UGD/008/E 500000156257		Rev. E		Page 2/2	