



Feature Stories



Heavy Duty &
Off-Highway
Vehicles
Emissions
Standards Guides

[Find by Feature](#)
[Browse by Category](#)
[Share](#)
 [Search →](#)

Part number or keyword

Search Results (0)

[Search Options](#)

Select a product type to narrow your search:

Terminal

Results with your selections: --

Blade size [mm]

Terminal family

Material

Sealing

Gender

Sealed

Inside Ring Diameter [mm]

Outside Ring Diameter [mm]

Minimum Cable Core Cross Section [mm²]

Maximum Cable Core Cross Section [mm²]

Minimum Cable Diameter [mm]

Maximum Cable Diameter [mm]

[Clear](#)

[Search →](#)

Female Metri-Pack 280 Tin Plated Terminal, Cable Range 0.50 - 0.35 mm², Cable Insulation Range 2.51 - 1.84 mm

Part #12052217

[Question about this product?](#)

[Attributes](#)

[Documents \(12\)](#)

Part #:	12052217
Description:	Female Metri-Pack 280 Tin Plated Terminal, Cable Range 0.50 - 0.35 mm ² , Cable Insulation Range 2.51 - 1.84 mm
Product Type:	Terminal
Status:	Active
Blade size [mm]:	2.8
Terminal family:	Metri-Pack
Series:	280
Gender:	Female
Sealed:	Unsealed
Material:	Tin Brass
Plating:	Tin
Minimum Cable Core Cross Section [mm²]:	0.35
Maximum Cable Core Cross Section [mm²]:	0.50
Minimum Cable Diameter [mm]:	1.84
Maximum Cable Diameter [mm]:	2.51