



Part Number : 1301080091

Series Number : 130108

Product Category : Lamps and Lights

Product Description : Super-Safeway 4W
Fluorescent Hand Lamp with Cord Ballast
Location and no Switch, Cord Type 18/3 SJTW,
Cord Length 5.49m (18.0')

Status : New Business Not Supported

Engineering Number : 1045

Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Lamps and Lights
Series	130108

Description	Super-Safeway 4W Fluorescent Hand Lamp with Cord Ballast Location and no Switch, Cord Type 18/3 SJTW, Cord Length 5.49m (18.0')
NEMA Configuration	NEMA 5-15
Product Family	Hand Lamps
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678861231

Electrical

Lamp Wattage - Maximum	4W
Lumens	95
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	5.49m (18.0')
Cord Length - Secondary	N/A
Cord Type - Primary	18/3 SJTW
Depth	31.75mm (1.250")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	N/A
Lamp Type	F4/T5
Length	342.90mm (13.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on May 06, 2024