


MMZ1608Y152CTA00



Applications	Commercial Grade
Feature	High Speed High speed signal line
Series	MMZ
Status	Production (Not Recommended for New Design) Recommended Alternate Part No. : MMZ1608Y152BTA00 (Interchangeability is not guaranteed.)
Brand	TDK





Size	
Length(L)	1.60mm ±0.15mm
Width(W)	0.80mm ±0.15mm
Thickness(T)	0.80mm ±0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics	
Impedance at 100MHz	1.5kΩ ±25%
Rated Current	300mA
DC Resistance (Max.)	500mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C
Soldering Method	Reflow
	Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	4000pcs
Weight	0.004g



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)





Associated Images

