



+ CONNECTORS

RECTANGULAR CONNECTOR HOODS



✓ Active

TE CONNECTIVITY (TE)
EMV24/64.STS.1.M40G
[HDC](#) | [HDC EMC Hood/Housing](#) , [HDC Hood & Housings](#)

1106461-2
TE Internal Number: 1106461-2

[EU RoHS Compliant with Exemptions](#)
[EU ELV Compliant with Exemptions](#)

Accessory Type Hood

Entry Style Side

Locking Device Type Screwlock

 **PRODUCT DRAWING**
[English](#)

 **3D PDF**

DOCUMENTATION

Product Drawings

HOOD EMV.24/64.STO/STS WITH M-THREAD

PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Accessory Type Hood

Product Size 8

Thread Size M40

Product Type Accessory

HTS Housings and Hoods Yes

Body Features

Entry Style Side

Color Gray

Material Aluminum

Mechanical Attachment

Locking Device Type Screwlock

Locking Device Location Hood

Dimensions

Height 90 mm [3.543 in]

Width 53 mm [2.087 in]

Length 156 mm [6.142 in]

Usage Conditions

Corrosion Protected No

Packaging Features

Packaging Quantity 5

Packaging Method Loose Piece

Other

Comment Protection against electro-magnetic interference, pressure-tight

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
