





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/22/08	
A		REDRAWN	10/17/11	
B		ADDED DIM.	10/21/20	AY/NP



Positions: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22, 24
A = .165 [4.20] X No. of Spaces per row
B = .165 [4.20] X No. of Positions per row + .055 [1.40]

SPECIFICATIONS:

Material:
Insulator: Nylon 66, rated UL 94V-0
Insulator color: Natural
Electrical:
Operating voltage: 600 VAC max
Current rating: / Circuit (See Chart)
Insulation resistance: 1000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1500 VAC for 1 minute
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant.

WIRE SIZE	CIRCUITS			
AWG	2	4~6	8~10	12~24
18	9 A	8 A	7 A	6 A
20	7 A	6 A	5 A	5 A
22	5 A	4 A	4 A	4 A
24	4 A	3 A	3 A	3 A



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			
.X ± .10	Ø.X ± .10		
.XX ± .020	Ø.XX ± .015		
.XXX ± .015	Ø.XXX ± .010		
APPROVALS		DATE	
DRAWN	DY	9/22/08	
CHECKED			
APPROVED			

ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
TITLE WIRE TO WIRE CONNECTOR HOUSING FEMALE, 4.2MM PITCH			
SIZE X	PART NO. DMH-XX-V0		REV. B
REF: S00123T	SCALE: NTS	SHEET 1 OF 1	