BPSF00131365470M00

Search by : Part Number Characteristics Cross reference



MP


Closed Magnetic Circuit Type

Series Pdf

Product detail	
L (mm) ±	12.5±0.3
W(mm) ±	12.5±0.3
T (mm) ±	6.5±0.35
Inductance(uH)	47
Tolerance(±%)	20
Test Frequency	0.5V 1kHz
RDC(ohm)	0.0578
RDC Tolerance(±%)	20
Isat(A)	2.4
Irms(A)	2.8

Part Numbering | Dimensions | Packing | Recommended Pattern | Electrical Characteristics

Downloaded from Arrow.com.



Products

Power Inductor

EMI-Noise Suppression

RF-Signal Inductor

Resistor & Current Sensor

Applications

Automotive

Industrial

Server/DataCenter

Communication

Mobile and Tablet

Computer/Laptop

Consumer

Design Tools

Simulation Tool

Product Search Engine

E-Catalogue

About Us

Corporate Overview

Corporate Milestones

Core Technology

Certificates & Awards

Quality and Social Responsibility

Investor

Financial Information

Corporate governance

Stakeholder Contacts

News

Media Center

New Products

Downloaded from Arrow.com.

Events

Product Notices

Contact Us

Contact Info

Contact Form

Join Chilisin

Terms of Use

Privacy policy

Sitemap



Inductor

Resistor

Powder

Copyrights © 2018. Chilisin. All rights reserved.

Downloaded from Arrow.com.