



Part Number : [190060005](#)
Product Description : Avikrimp Quick Disconnect, Female Flag, for 22-18 AWG (0.80-0.35mm²) Wire, Tab 4.75 x 0.51mm, Red, Bag
Series Number : 19006
Status : Active
Product Category : Quick Disconnects
Engineering Number : AA-5222



Documents & Resources


Drawings
[190060005_sd.pdf](#)

3D Models and Design Files
[190060005_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)
[PS-19902-014-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19006
Description	Avikrimp Quick Disconnect, Female Flag, for 22-18 AWG (0.80-0.35mm ²) Wire, Tab 4.75 x 0.51mm, Red, Bag
Product Name	Avikrimp
Type	Quick Disconnect
UPC	800753030961

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-2
Gender	Female
Glow-Wire Capable	Yes
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.279/g
Orientation	Flag
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	3.81mm max.
Wire Size (AWG)	18, 20, 22

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp Fully Pre-Insulated and Insulated Quick Disconnect Flags, 22-14 AWG	<u>640014300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640054300</u>

This document was generated on Mar 12, 2025