

© 2020 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRWAING	13MAY2020	GK	DB

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inch]

TE PN: D12463-000

OUTSIDE WOUND (BACK SLIT CENTRED)
LABEL ACROSS: 1
PER ROLL QTY: 54.86m / 180 feet

MATERIAL	POLYVINYL FLUORIDE (TEDLAR®)
ADHESIVE TYPE	PERMANENT ACRYLIC
LINEAR	BROWN KRAFT

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	−0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL: SEE TABLE

FINISH: GLOSS

DWN 13MAY2020 GOPALAKRISHNA_HV
CHK 13MAY2020 D.BURGAT
APVD 13MAY2020 D.BURGAT
PRODUCT SPEC: TTDS–005
APPLICATION SPEC: —
WEIGHT: 95g

TE Connectivity

NAME: TEDLAR® LABEL–WHITE–CONTINUOUS–WITH TRACTOR FEED 12.7mm x 54.8m (0.5inch x 180ft)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	FB1U7	C–TTVF050WE–180	—

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 1 | REV A

TTVF050WE–180

1471–9 (1/15)

Downloaded from Arrow.com.