

Development Tools ADM00931

Reorder

: 0 Item(s) - USD 0

Clear All

Results 1 - 1 of 1 for "ADM00931"

View 50 per page

Search results in All Categories



Part Number: ADM00931 - HV892DB1 Liquid Lens Driver Demo Board

The HV892DB1 liquid lens driver demoboard is controlled via an I2C interface and is capable of driving capacitive loads of up to 200pF, and is compatible with 40VRMS to 60VRMS lenses. A charge pump boost converter integrated on-chip provides the high voltage necessary for driving the lens. No external inductors or diodes are needed.

BACK TO TOP FEEDBACK

*ASEAN countries not listed +632 - 479 2850	*European countries not listed 0 800 056 5113	Australia 1 800 193 884	Austria 0 800 298 364	Belgium 0 800 78 586	Bulgaria 00800 210 0073
Canada 1-888-624-7435	China 10 800 140 2127	Croatia 0800 890 094	Czech Republic 800 090 425	Denmark 802 53233	Estonia / Lithuania / Latvia 8 800 3 31 17
Finland 0 800 917 739	France 0 800 900 990	Germany 0 800 180 0121	Greece 00 800 161 2203 0248	Hong Kong 800 960 674	Hungary 06 801 099 86
Iceland +45 4450 2827	India 000 800 1009 343	Ireland 1 800 901 628	Israel 1 80 945 0151	Italy 800 786 648	Japan +81 3 6880 3745
Latin America 1-888-624-7435	Moldavia 0 800 61527	Netherlands 0 800 022 4021	New Zealand 0 800 480 421	Norway 800 690 17	Philippines 180011102092
Poland 00 800 112 47 69	Portugal 800 819 068	Romania 0 800 896 371	Russia 8 800 301 7156	Slovakia 0 800 606 095	Slovenia 0 800 81772
South Africa 0 800 981 024	South Korea 0 82 2 554 7200	Spain 900 808 071	Sweden 0200 99 0585	Switzerland 0 800 895 951	Taiwan 00 801 127 676



OK