

Part Number : 1300660054
Product Description : BradPower A-Size (7/8”–M22) Receptacle, 3 Poles, Male, Single Keyway, 1/2" - 14 NPT, 14/1 AWG, 2.0m (6.56') Length
Series Number : 130066
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : 1R3006A28M020G

Documents and Resources

Drawings

1300660054_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(a)-I; 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130066
Description	BradPower A-Size (7/8”–M22) Receptacle, 3 Poles, Male, Single Keyway, 1/2" - 14 NPT, 14/1 AWG, 2.0m (6.56') Length
IP Rating	IP67
Product Name	BradPower A-Size
Type	Single Ended (pigtail)
UPC	78678880933

Agency

UL	E258922

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	2.0m
Material - Component	Black Annodized Aluminum
Mounting Thread Size	1/2" - 14 NPT
Net Weight	522.000/g
Orientation	Straight
Panel Mount	Front
Poles	3
Temperature Range - Operating	-20° to +105°C

Downloaded from Arrow.com.

Wire/Cable Type	UL 1015
Wire Size (AWG)	14

Downloaded from Arrow.com.