

Han® S 120 FC CRT 10 mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 8260
Specification	Han® S 120 FC CRT 10 mm ²
HARTING eCatalogue	https://b2b.harting.com/09930008260

Identification

Category	Contacts
Series	Han® S
Identification	Han® S 120
Type of contact	Crimp contact
Description of the contact	Female contact

Version

Manufacturing process	Turned contacts
Details	Using of rubber sleeve is imperative! Please order separately.

Technical characteristics

Conductor cross-section	10 mm ²
Conductor cross-section	AWG 8
Rated current	≤120 A
Contact resistance	≤0.3 mΩ
Stripping length	22 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant
China RoHS	e

Page 1 / 2 | Creation date 2024-02-10 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Net weight	18.4 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140188747
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors